BUCKLEYS DATA SHEET H28 CALIBRATION KIT





FEATURES

- Easy to use
- All kit parts can be replaced individually
- Full instructions included

Calibration Kit (ref: H28) comprises:

BCM Checker, 3 x screw-on K-Series reference electrode cells, sea water corrosion test mixture, full instructions for "in-house" calibration.

ANCILLARY PRODUCTS AVAILABLE

Replacement Silver/Silver Chloride screw in half cell (our ref: H6)

Sea water corrosion test mixture (our ref: H26) Adaptor leads for K-Series reference cell (our ref: H16) The Calibration Kit has been created to provide all the necessary components to enable customers to verify the accuracy of the readings on the Buckleys or Roxby Bathycorrometers so that "in-house" calibration certificates can be issued.

The process requires two areas to be checked. The electronics should be tested using the BCM Checker. Readings on the Bathycorrometer should be 0.000 with the checker switched off and 1.990 with the checker on.

Providing the readings are correct, the Silver/Silver Chloride screw-in half cell should be checked by using K-Series Reference Cells in a standard salt water solution. To confirm the readings, three cells should be used and the Sea Water corrosion test mixture should be made up to a 3% solution.

TECHNICAL SPECIFICATION BCM Checker

- Power Supply: 9 volt battery (PP3)
- Battery Type: Alkaline MN1604
- Output Voltage: 1.990 Volts
- Accuracy: +/- 0.01%
- Temperature coeff: 30ppm/°C
- Temperature range: 0-30°C
- On indicator: Green LED
- Low battery indicator: Red LED
- Connection: 5 pin plug & probe clip

K-Series Reference Cell

- Electrical Connection: screw fit
- Output: +208mV @ 25°C vs SHE
- Accuracy: ±5mV @ 25°C vs SHE
- Temperature coeff: -0.64mV per/°C
- Temperature range: 0 40 °C
- Working life: up to 1 year
- Dimensions: 155mm long x 25mm diam.
- Packed weight (Calibration kit): 1.2Kg
- Dimensions (packed): 26cm x 14cm x 30cm

Note: Due to ongoing technical developments, all stated information is typical and subject to change without notice or obligation

AFTER SALES SERVICE / TECHNICAL SUPPORT

All Buckleys products are manufactured under the controls established by a quality management system that meets the requirements of BS EN ISO 9001:2008 and are supplied with a one year "back-to-base" warranty. The equipment is proven to be robust and reliable and will give years of service if maintained in accordance with our instructions.

Annual re-calibration is recommended for Bathycorrometers. Buckleys provide full repair and calibration facilities offering a fast turn-around service for customer's equipment.

Advice on specific applications for all Buckleys products is available from our technical department. Contact us by telephoning, sending a fax or by e-mail using the contact details below.

Buckleys (UVRAL) Ltd., Buckleys House, Unit G, Concept Court, Shearway Business Park, Shearway Road, Folkestone, Kent. CT19 4RG. UK Tel: +44 (0)1303 278888 Fax: +44 (0)1303 274331 e-mail: sales@buckleys.co.uk web site: www.buckleys.co.uk 1012